

# Product Data Sheet

## Little Digital Precision Scale

Reference 97000-001-ca

## Specifications

- Maximum capacity : 1 000 g
- g/ oz / gn / ct / tl / ozt / dwt
- Accuracy : 0.1g
- Self calibration - Backlight
- Auto off after 60s
- Size : 127 x 76 x 20 mm
- Weight : 132 g.
- Use 1.5V. batteries x 2 AAA model
- In box, with instructions



*french cooking by* 



Avoid any exposure to extreme heat or cold. Your scales work better when operated at normal room temperature for at least one hour before use. Give your scales sufficient warm up time (30 seconds) to give the internal components a chance to stabilize. Keep your scales in a clean environment. Only operate the scales on a stable, vibration-free surface.

## Instructions

### OPERATION

- Place the scales on a horizontal, flat surface, press the [ON/OFF] to turn on the scales.
- Wait until "0.0" is displayed.
- Put the object(s) on the weighing platform.
- Use the [MODE] to change the unit of measurement.

### TAREWEIGHING

- Turn on the scales.
- Place the container on the platform.
- Press [TARE] and wait until "0.0" or "0.00" is displayed.
- Add the content to weigh.

### CALIBRATION

- Turn on the scales by pressing the [ON/OFF].
- Wait until the LCD displays "0.0" or "0.00" and then press the [CAL]. The LCD will display "CAL".
- Press the [CAL] key again. The LCD will display « CAL » followed by the required calibration weight.
- Add the required calibration weight. The display will show "PASS" and return to normal weighing mode.
- Put away the calibration weight and press [ON/OFF] to turn off the scales. The calibration is complete.

Alla France

Z.I. du Bompas - 13, rue du Bompas - Chemillé - 49120 Chemillé-en-Anjou - FRANCE

Tél. + 33 (0)2 41 30 55 08 - Fax +33 (0)2 41 30 34 67

[www.allafrance.com](http://www.allafrance.com)

  
France